



GREENLEE®
A Textron Company

MADE FOR THE TRADE!™



BENDER, ELECTRIC CONDUIT

854DX Electric Bender

Cat No: 52067299

UPC No: 783310026709

Description

- VERSATILE - 1 shoe bends ½" to 2" EMT, IMC and Rigid conduit
- ACCURATE - Absolute encoder stops bending at precise angles
- RELIABLE - Solid state electronics rated for 1,000,000+ bends
- Simple switching between vertical and horizontal bending configurations
- Digital pendant sets angle and monitors process
- Solid state system eliminates arcing and prevents damage from temporary power loss

Specifications

- Accessory : 02840 Shoe Group, 1/2" to 2" PVC Coated Rigid (854DX)
- Amperage Rating : 20 AMP GFCI Protected Receptacle
- Application : Conduit bending
- Bend Radius : 4.25" (108 MM) - 9" (228.6MM) (EMT, IMC Rigid) For 1/2" - 2" Shoe Size
- Capacity : 1/2" - 2" Rigid, IMC, EMT
- Includes : 1/2" - 2" Rigid / EMT / IMC Shoe, Roller Support and Digital Pendant
- Standard : C/US UL Listed
- Type : Electric Conduit Bender
- Voltage Rating : 120 VAC
- Weight : 550 lbs