



- Lamps
- Ballasts
- Luminaires
- Company
- Customer Care
- Contact Us

Search > Results for 45504 > CFL105/50/E39/277V 45504 105W 277V T5 SPIRAL 5000K MOG PROLUME



CFL105/50/E39/277V 45504 105W 277V T5 SPIRAL 5000K MOG PROLUME

Product Number: 45504
UPC: 807154455041

[Log In for Price and Availability](#)

Specifications	Resources	Technical
Applications	Warehouse; Gymnasiums; High Bays; Low Bays	
Average Life (Hrs)	10000	
Base	Mogul	
Brand	ProLume	
Bulb	T5	
CRI	82	
Color Temperature	5000	
Dimensional Dwg		
Dimmable	No	
ENERGY STAR	No	
Equivalent Wattage	500	
HTS code	8539310070	
Initial Lumens	7000	
Inner Carton Quantity	1	
Input Frequency (Hz)	60	
Markets	Residential, Commercial	
Master Carton Quantity	6	
Maximum Overall Diameter	4.02	
Maximum Overall Length	11.25	
Nominal Length	11.25	
Operating Position	Universal	
Prod Code	CFL105/50/E39/277V	
Product Category	CFL Self-Ballasted	
Product Description	105W 277V T5 SPIRAL 5000K MOG PROLU	
Product Number	45504	
Start Type	Instant Start	
Voltage (V)	277	
Warranty (Yrs)	1	
Wattage (W)	105	

Products

Lamps



Ballasts



Luminaires



Resources

- Catalogs
- Sell Sheets
- New Products

Contact Us

Corporate Office:
Halco Lighting Technologi
2940 Pacific Drive
Norcross, GA 30071
Toll Free: 800.677.3334
Office: 770.242.3612
Fax: 800.880.0822
Email: customer@halco.com

Top

