



Powering Business Worldwide

pe.eaton.com

Type GHB Bolt-On Panelboard Circuit Breaker

GHB2050

UPC: 786679911235

Dimensions: 3.9 IN * 2.3 IN * 4.8 IN (L * W * H)

Notes: No Data

Warranty: Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Molded case circuit breaker
- **Mounting:** Bolt-on
- **Frame Size:** G-frame
- **Series:** Series C
- **Trip Type:** Non-interchangeable thermal-magnetic
- **Amperage Rating:** 50A
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 480Y/277V

Supporting documents:

- [MOEM MCCB Product Selection Guide Brochure](#)
- [Eatons Volume 4-Circuit Protection Catalog](#)
- [G-frame Molded Case Circuit Breaker Drawing Drawing](#)
- [Series C GB/GHB/GDB Circuit Breakers - IL Inst Leaflet](#)
- [Series C G-Frame Time Current Curves Specification](#)
- [Type GHB/GHC/GD/GPS 2 and 3-pole, 15-100A Time Curve Time Curr Curve](#)

Certifications:

- UL Listed



Product compliance:

- Federal Specifications Classification W-C375B

© 2016 Eaton. All rights reserved.