



Hoffman

HOL-SEALERS Hole Seals

Catalog Number: AS300
US List Price (USD): \$30.04

Bulletin Number:

- A80HS

Material:

- Steel



Model Code:

- 59780

Ship Wt. Std. Pkg. (lbs):

- 6.0

Interchangeable:

- False

Finish Color:

- ANSI 61 gray

Industry Standards:

Steel Hole Seals UL 508A Component Recognized; Type 3R, 4, 12, 13; File No. E61997 CSA File No. 42186; Type 3R, 4, 12, 13 NEMA/EEMAC Type 3R, 4, 12, 13 IEC 60529, IP66 **Stainless Steel Hole Seals** UL 508A Component Recognized; Type 3R, 4, 4X, 12, 13; File No. E61997 CSA File No. 42186; Type 3R, 4, 4X, 12, 13 NEMA/EEMAC Type 3R, 4, 4X, 12, 13 IEC 60529, IP66

Description

Applications:

Seal extra pushbutton holes, conduit openings and knockout openings against dust, dirt, oil and water with Hoffman HOLSEALERS™. Seals will cover any size or shape of hole from .19-in. diameter to maximum diameter shown in table. Can be used on enclosure walls up to .31-in. (8-mm) thick.

Features:

- Available in multiple colors and sizes
- Oil-resistant gasket provided

Specifications:

- Steel Models:
 - 16 gauge galvanized steel backplate
 - Plated stud (10-32x5/8) and wing nut
- Stainless Steel Models:
 - 16 gauge stainless steel backplate
 - Seal, backplate, stud (10-24x5/8) and wing nut are 300 series stainless steel

Finish:

- Steel seals have polyester powder paint finish over galvanized front surface.
- Stainless steel seals have polished front surface.

Technical Data

HOL-SEALERS Hole Seals

Catalog Number	AS300
For	3-in. conduit holes
Maximum Hole Diameter in.	3.62
Hol-Sealer Diameter in.	4.12

Certifications



EU Certification

Documents



3D STEP CAD



2D DXF CAD



Spec Sheet

No accessories available.