



Shrink-Kon[®]

Splice Insulators and Insulating Covers
T&B Catalog Number:

UPC Number: MSC2
Status: 78621081767
Description: Active

Motor Stub Splice Insulator 12 - 8 AWG

Features

Re-enterable motor stub insulator.
 Easy installation. No special tools required.

General

Style Motor Stub Splice Insulator
Color Black
Temperature Range 90°C

Dimension Information

A (inches) 3.25
B (inches) 0.947
C (inches) 0.877
Cable Range 12 - 2 AWG
Standard Length (inches) 0.75

Specifications

Voltage Rating 600V
Flammability Rating UL 94 V-1

Packaging

T&B Order Multiple 10
T&B Inner Pack 10
Package in Units 30
T&B Sold in UOM Each
T&B Weight Per UOM 13.5 lbs. per 100

Application Support

Specifications Available on Website
Overview Available on Website

Notes

Order multiple is standard package.

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
 E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289

