



Actual

Catalog Number: HUB3/4SA-G
Product ID: 7TAA087850R0002
UPC Number: 70450838867
EAN Number: 05415022251418
Status: Active

PVC Coated Aluminum Hub Connector with Thermoplastic Insulated Throat, Pipe Size 3/4 Inch/21 Metric, Overall Diameter 1.44 Inch/36.58 Millimeters, Maximum Panel Thickness 0.19 Inch/4.83 Millimeters, Throat Diameter 0.78 Inch/19.81 Millimeters, Nitrile Rubber (Buna-N) Sealing Ring, Dark Gray

- Coated with a nominal .002 inch (2 mil) blue urethane on the interior, before PVC Coating is applied.
- A minimum .040 inch (40 mil) PVC Coating is bonded to the exterior.
- Innovative sealing ring and groove.
- Hexagonal body and locknut design.
- Insulated throat and sharper and deeper teeth.
- Pressure sealing sleeves to protect the connection.

UNSPSC Specifications

UNSPSC	39121311 Electrical fittings
IGCC	4441 Electrical fittings
Brand Name	Ocal
Type	Hub Connector
Special Features	Hexagonal/Splined Body and Locknut Enables Fast and Easy Installation
Application	To Positively Bond Conduit to Box or Enclosure
Size	3/4 Inch/21mm
Material	PVC Coated Aluminum
Color	Dark Gray
Temperature Rating	105 Degrees C

Packaging

Inner Dimensions (inches)	xx
Outer Quantity	50
Outer Dimensions (inches)	12x7x7
Weight Uom	15 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website
Support/Tools 1	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com