



Color-Keyed®

Splice Connector

T&B Catalog Number:

54815

UPC Number:

78621054815

Status:

Active

Description:

Copper Two-Way Splice, Long Barrel, Max 35kV, 350 kcmil, Tin Plated, Die Code 71, Die Color Red

Features

Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

General

Style	Two-Way Long Barrel Splice
Material	Copper
Finish	Tin-Plated
Wire Size	350 kcmil
Wire Size Flex	650/24 = 262 kcmil
Die Color	Red
Die Code	71

Dimension Information

A (inches)	3.75
E (inches)	0.95

Specifications

Voltage Rating	600V
----------------	------

Packaging

T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	28.5 lbs. per 100

Application Support

T&B Instruction Sheets	ta00674-tb2
------------------------	-------------

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

Y

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com