



Representative

Catalog Number: 54804
Product ID: 7TAH007510R0000
UPC Number: 78621054804
EAN Number: 05414363110712
Status: Active

Copper Two-Way Splice, Long Barrel, Max 35kV, Wire Size #8 AWG, Length 1.75 Inches, Diameter 0.27 Inches, Silver Plated, Die Code 21, Die Color Code Red

- Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Color-Keyed
Type	Splice Connector
Special Features	Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.
Standard	UL E9809
Material	Copper
Finish	Tin-Plated
Color	Red
Voltage Rating	600V

European Specifications (ETIM)

ETIM	EC001059 Crimp splices for copper conductor
Sleeve form	Long
Material	Copper
Insulation	None
Voltage row	Up to 35kV

Packaging

Inner Quantity	50
Inner Dimensions (inches)	3.3x2.8x2.3
Outer Quantity	500
Outer Dimensions (inches)	12.5x6.4x4
Weight Uom	2 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website
Instruction Sheet 1	ta00674-tb2

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com