



OL11201DWZ: 18" LED Outdoor Sconce



Dimensions:

Width: 5" **Extends:** 3 3/8"
Height: 17 1/2" **Wire:** 8"
Mounting Proc.: Cap Nuts
Connection: Mounted To Box
Bulb Type: Array
Bulb Base: Integrated
Volts: 120
Watts: 22
Watts Consumed: 22
Watts Rated: 22
Hours Rated: 30000
Lumens: 1600
Bulb Temp: 2700 °K
CRI: 90

Features:

- Meets American with Disabilities Act standard extension requirements
- This advanced LED technology is carefully designed and selected to consist of the highest quality LED chipsets for superior performance and reliability.

Material List:

1 Body - Steel - Dark Weathered Zinc

Safety Listing:

Safety Listed for Wet Locations

Instruction Sheets:

Trilingual (English, Spanish, and French)
 (OL11200_OL11201_OL11202_OL11203_)

Collection: Ledgend

UPC #:014817541205

Finish: Dark Weathered Zinc (DWZ)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Diffuser	Glass	White	1									

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	OL11201DWZ	1	014817541205	22	9.5	10.5	1.27	6.2	150	Yes
NJ Pallet		56		48	40	77	85.556	347.2		No
NV Pallet		56		48	40	77.75	86.389	347.2		No