



GE
Lighting

93360 - null

LED7DP203W827/20

Product Photo



GENERAL CHARACTERISTICS

Product Technology	LED
Rated Life (Hours)	25000 h
Base	E26

PHOTOMETRIC CHARACTERISTICS

Beam Spread (range)	20 deg
Center Beam Candle Pwr Candela	3600 cd
Nominal Initial Lumen per Watt	71.4
Rated Beam Spread	20 deg
Initial Lumens-nominal	500 lm
Color Rendering Index-CRI	80
Color Temperature	2700 K

PRODUCT INFORMATION

Product Code	93360
Description	LED7DP203W827/20
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168933605
Standard Package GTIN	10043168933602
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168933605
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168933605
Standard Package GTIN	00043168933605
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168933605

DIMENSIONS

Bulb Max Overall Length-MOL	3.5 in
-----------------------------	--------