



Color-Keyed®

Splice Connector
T&B Catalog Number:

54805
 78621054805
 Active

UPC Number:
Status:
Description:

Copper Two-Way Splice, Long Barrel, Max 35kV, Wire Size #6 AWG, Length 1.75 Inches, Diameter 0.31 Inches, Tin Plated, Die Code 24, Die Color Code Blue

Features

Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.



General

Style	Two-Way Long Barrel Splice
Material	Copper
Finish	Tin-Plated
Wire Size	#6 AWG
Wire Size Flex	61/24 = 24.6 kcmil
Die Color	Blue
Die Code	24

Dimension Information

A (inches)	1.75
E (inches)	0.31

Specifications

Voltage Rating	600V
----------------	------

Packaging

T&B Inner Pack	50
Package in Units	500
T&B Sold in UOM	Each
T&B Weight Per UOM	2 lbs. per 100

Application Support

T&B Instruction Sheets	ta00674-tb2
------------------------	-------------

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:
 Y

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com