



Representative

**Catalog Number:** 54808  
**Product ID:** 7TAH007510R0007  
**UPC Number:** 78621054808  
**EAN Number:** 05414363110750  
**Status:** Active

Copper Two-Way Splice, Long Barrel, Max 35kV, Wire Size 1 AWG, Length 2.0 Inches, Diameter 0.49 Inch, Tin Plated, Die Code 37, Die Color Code Green

- Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

#### North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Color-Keyed
Type	Splice Connector
Special Features	Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.
Standard	UL E9809, CSA 4503
Material	Copper
Finish	Tin-Plated
Color	Green
Voltage Rating	600V

#### European Specifications (ETIM)

ETIM	EC001059 Crimp splices for copper conductor
Sleeve form	Long
Material	Copper
Surface protection	Tinned
Insulation	None
Voltage row	Up to 35kV

#### Packaging

Inner Quantity	20
Inner Dimensions (inches)	3.3x2.8x2.3
Outer Quantity	200
Outer Dimensions (inches)	12.5x6.4x4
Weight Uom	4.88 lbs. per 100

#### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website
Instruction Sheet 1	ta00674-tb2

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com