



Color-Keyed®

Splice Connector
T&B Catalog Number:

54810
78621054810

UPC Number:

Status:

Active

Description:

Copper Two-Way Splice, Long Barrel, Max 35kV, 2/0 AWG, 275/24, Length 2.13 Inches, Tin Plated, Die Code 45, Die Color Code Black

Features

Two-way connectors provide high pullout values, are easy to insulate and provide a low-resistance connection of high quality and low installed cost.

General

Style	Two-Way Long Barrel Splice
Material	Copper
Finish	Tin-Plated
Wire Size	2/0 AWG
Wire Size Flex	275/24 = 111 kcmil
Die Color	Black
Die Code	45

Dimension Information

A (inches)	2.13
E (inches)	0.59

Specifications

Voltage Rating	600V
----------------	------

Packaging

T&B Order Multiple	10
T&B Inner Pack	10
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	7 lbs. per 100

Application Support

T&B Instruction Sheets	ta00674-tb2
------------------------	-------------

Notes

UL Listed for direct burial applications.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

Y

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.

T&B Technical Support
MS 3B-50

Hours: 7AM - 6PM CDT
Monday-Friday

Memphis, TN 38125
www.tnb.com

8155 T&B Blvd.
Memphis, TN 38125

Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com