



Product Specifications for E41050-PLPC

Job Name:	Job Type:
Quantity:	Comments



E41050-PLPC Eco-Task LED Floor Lamp

Finish

Platinum / Polished Chrome

Glass/Shade

Product Category

Floor Lamp

Lamping

Number of Bulb(s)	N/A
Light Type	LED
Bulb Type	LED
Max Bulb Wattage	28+6
Max Fixture Wattage	34
Rated Life	±40,000 Hours
Rated Lumens	±2,750
Color Temp	N/A
Bulb(s) Included	Integrated
Light Up/Down	N/A
Beam Spread	N/A
CRI	N/A
Photo Cell Included	N/A
Ballast/Driver/Transformer	No
Dimmable	Built In

Measurements

Width	13.00"
Height	72.00"
Length	13.00"
Extension	N/A
Back Plate Width	N/A
Back Plate Height	N/A
HCO	N/A
Min Overall Height	N/A
Max Overall Height	N/A
Hanging Weight	23.00 lb(s)
Height Adjustable	N/A
Slope	N/A
Chain Length	N/A
Wire Length	N/A
Canopy Width	N/A
Canopy Height	N/A
Canopy Length	N/A

Shipping

Carton Weight	26.18 lb(s)
Carton Width	5.90"
Carton Height	42.32"
Carton Length	15.35"
Carton Cubic Feet	N/A
Master Pack	1
Master Pack Weight	N/A
Master Pack Width	N/A
Master Pack Height	N/A
Master Pack Length	N/A
Master Cubic Feet	N/A
UPS Shippable	Yes

Certification

Safety Rating	Dry
Energy Star	No
CA Title 24	No
CA Title 20	No
ADA	No

Other

UPC Code	845094070146
Material	N/A

Equivalents

Incandescent Watts	N/A
Fluorescent Watts	N/A

ET2 Contemporary Lighting and all designs, logos and images © 2015 ET2 Contemporary Lighting. All Rights Reserved. ET2 Contemporary Lighting reserves the right, at any time, to make changes in the design and/or construction of the product including the discontinuation of product without prior notice. Color may vary from what is pictured above due to limitations inherent to photographic processes. Always consult a qualified, licensed electrician before installation of any product weighing 35 pounds or more. We recommend that a qualified, licensed electrician do the installation. Always install to a mechanically sound structure.