



Item #: **F622-PW**
 Product Family Name: **Traditional Mojo**
 Category: **Interior Fan**
 Certification: **4000048**
 Patents:
 Notes:

UPC Code: **706411052408**
 Finish: **Pewter**
 Category Type: **Ceiling Fan**

Image File Name:
 F622-PW--
 1422960545.jpg



MEASUREMENTS

Blade Finish: Reversible Blades: **No**
 Blade Material: **PLYWOOD CONSTRUCTION**
 Blade Sweep: **52** No. of Blades: **5** Blade Pitch: **12 DEGREES** Hanging Weight: **17.11**
 Downrod 1: **3.5** Downrod 1 Outside Dia.: **.75** Downrod 2: **6** Downrod 2 Outside Dia.: **.75**
 Ceiling to Lowest Point: (Dim A) **15.00** Ceiling to Blade: (Dim B) **9.50** Lead Wire: **80** Motor Size: **153x15mm**

	Low:	Low/Med:	Medium:	Med/High:	High:
RPM:	79		133		188
Amps:	0.27		0.42		0.56
Watts:	13.700		33.800		66.100
CFM:	2527.00		4065.00		5699.00
CFM/Watts	184.45		120.27		86.22



FAN CONTROLS

Pull Chain Control: **Yes** Works with Remote Control: **Yes** Works with Wall Control: **Yes**
 Included Remote Control: **Compatible Remote Control[s]: RCS223** Included Wall Control: **Compatible Wall Control[s]: WCS223,WC106**

LAMPING

No. of Bulbs: **3** Light Type: **B10.5,Cand**
 Max Bulb Wattage: **60** Socket: **E12**
 Light Kit: **Yes** Dimmable: **No** Ballast: **Yes** Rated Life Hours: **10000** Uplight: **No**
 Lamp Included: **Yes** Color Temp.: **2700K** CRI: **90** Initial Lumens: **2700** Delivered Lumens: **2700**

GLASS

Description: **Glass** Material: **Glass**
 Part No.: **1422960545** Quantity: **1**
 Width: **14.5** Height: **14.5** Length: **14.5**



SHIPPING

Carton Width: **13.250** Carton Height: **10.500** Carton Length: **22.750**
 Carton Weight: **20.350** Carton Cubic Feet: **1.832** Small Package Shippable: **Yes**
 Master Pack Width: **13.250** Master Pack Height: **10.500** Master Pack Length: **22.750**
 Master Pack Weight: **20.350** Master Cubic Feet: **1.832** Multi-Pack: **1** Master Pack: **1**



ETL Intertek

Yes