

FEISS

EST. 1955

Job Name:

Job Type:

Comments:

Quantity:

F3020/3SN: 3 - Light Chandelier



Dimensions:

Diameter: 21 1/2"
Height: 18 3/4"

Overall Height: 63 3/4"
Wire: 180" (color/Black/White)
Connection: Mounted To Box

Bulbs:

3 - Medium A19 75w Max. 120v - Not included

Features:

Material List:

1 Body - Steel - Satin Nickel
 1 6" Stem - Steel - Satin Nickel
 3 12" Stem - Steel - Satin Nickel

Safety Listing:

Safety Listed for Dry Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (F3018-3_F3020-3_F3022-3)

Collection: Hobson

UPC #: 014817537635

Finish: Satin Nickel (SN)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Glass	Glass	Clear Seeded	3									

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	FrL Class	UPS Ship
Individual	F3020/3SN	1	014817537635	23.5	17	16.5	3.815	13.4	250	Yes
NJ Pallet		20		48	40	70.5	78.333	268		No
NV Pallet		20		48	40	70.5	78.333	268		No