



46546

F32T8 TL841/HV/ALTO (PK X 30)



Application: Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting

Base: Medium Bi-Pin (G13)

Coating: Copolymer

Color Temperature: 4100

Diameter: 1.00 IN

Lamp Type: Fluorescent

Mean Design Lumens: 2710

Shape: T

Type: Straight Linear Fluorescent Lamp

Wattage: 32.0 W

Average Life Hours: 36000

Bulb: T8

Color: TL841

CRI: 85

Initial Lumens: 2850

Length: 48.00 IN

Pack By: 30

Special Features: Shatter-Resistant

UPC: 726585465460

UL® Listed, NSF Approved