



S9354

54W/LED/HID/5000K/100-277V

54 watt - HID Replacement; 5000K; Mogul base; 100-277 volts

Features

- High Lumen Omni-directional LED for Industrial / Commercial applications
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- UL approved for totally enclosed fixtures
- Damp location - IP64 rated
- Base up, base down or horizontal operation
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- cULus listed

Additional Technical Specifications

- Power Factor >0.9
- Operating temperature range -20°C to 65°C
- Operating Frequency 50-60Hz
- Working Voltage AC90-305V

Optional accessory: In-line surge protector [80-929](#)

This item has been discontinued.

Suggested replacement:

- [S9394](#)



S9354

Item Number	Product Line	UPC	Input Voltage	Watts	Incandescent Equivalent	Fluorescent Equivalent	HID Equivalent
S9354	Hi-Pro	045923093531	100 - 277	54	300W	85W	250W

Base	ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens
Mogul	E39	54W/LED/HID/5000K/100-277V	Non-Dimmable	White	10.47"	3.69"	6480

Average Rated Hours	Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type
---------------------	-------------	-------	-----	-----------------	-----------------------	------	--------------

40000	5000	Natural Light	80+	300	-20C (-4F) to a maximum of +65C (+149F)	12	Box
RoHS Compliant	UL or ETL Listed		Warranty		Status	Suggested Substitute	
Yes	Yes		5 Year Limited		Discontinued	S9394	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051