

Above: LARC6 Fixture.
 Right: LARC6 with Rigid Inline Power Switch (LARC6-MS-W) Far Right: LARC6 with Rigid Inline Touch Dimmer (LARC6-TD-W) Sold individually.

PRODUCT DESCRIPTION

LARC6 24VDC Architectural LED Linear Lightbar is an 8", 16", 24" or 32" white, rigid and unobtrusive (only 3/8" thickness) dimmable LED LightBar. LARC6 can be interconnected in series from one 24VDC power source. Only 3W for 8", 6.5W for 16", 10W for 24" and 13W for 32". 80+ CRI and 50,000 hour LED life. Designed for cove lighting, commercial and architectural applications.

PROJECT	TYPE
CATALOG NUMBER	

KEY FEATURES

- Unique design - extruded aluminum vessel with frosted polycarbonate lensing
- Modular design - available with wide variety of connectors and accessories (see below)
- Mounts via 2 adjustable mounting hinges
- Touch dimmer

ELECTRICAL

- 24VDC
- Rated at 5.0W per foot
- 8": 3W, 16": 6.5W, 24": 10W, 32": 13W
- Rated Life: 50,000 hrs.

NOTE: Use non-dimmable power supplies with touch dimmer. Without touch dimmer you are free to use other dimmable power supplies.

OPTICS

- 3000K
- Up to 1100 lumens per bar
- 80+ CRI

CERTIFICATION



- ETL

WARRANTY


- 5 year warranty



OVERHEAD VIEW



SIDE VIEW



ANGLE MOUNT VIEW

FIXTURE ORDERING INFORMATION

Catalog No.	Length	Wattage	Lumens	Kelvin Temp.*	Finish	LED Life
LARC6-8-WW-W	8"	3W/bar	200/bar	3000K	White	50,000 hrs.
LARC6-16-WW-W	16"	6.5W/bar	450/bar	3000K	White	50,000 hrs.
LARC6-24-WW-W	24"	10W/bar	720/bar	3000K	White	50,000 hrs.
LARC6-32-WW-W	32"	13W/bar	1100/bar	3000K	White	50,000 hrs.

Includes (2) mounting clips with screws, (1) lightbar to power supply connector (GMC-PS-24-W) and (1) rigid bar to bar connector (LARC6-BB-1-W) included with each lightbar.

* Kelvin temperature (color) ±200K

ACCESSORY ORDERING INFORMATION

Cat. No.	Description
DPSP-4-W	4 port splitter block - white
DPSP-8-W	8 port splitter block - white
GMC-MM-3-W	3" male to male flexible cable connector - white
GMC-MM-6-W	6" male to male flexible cable connector - white
GMC-MM-12-W	12" male to male flexible cable connector - white
GMC-MM-24-W	24" male to male flexible cable connector - white
GMC-MM-39-W	39" male to male flexible cable connector - white
GMC-MM-60-W	60" male to male flexible cable connector - white

Cat. No.	Description
GMC-FF-3-W	3" female to female flexible cable connector - white
GMC-PS-24-W	24" lightbar to power flexible connector - white
GMC-PS-48-W	48" lightbar to power flexible connector - white
GMC-PS-60-W	60" lightbar to power flexible connector - white
LARC6-TD-W*	Rigid inline touch dimmer - white rigid
LARC6-MS-W	Inline master power switch - white rigid
LARC6-OS	Inline occupancy sensor, adj. angle and timing - white rigid
GMSB-W(B)	Splice box - white (black) - 2"L x 1"W x 5/8"D

* Use only non-dimmable power supplies with LARC6-TD-W