



S9216

9.8A19/OMNI/300/LED/2700K/GU24
9.8 watt; A19 LED; Frosted; 2700K; GU24 base; 300' beam spread; 120 volts

Features

- Solid State LED lighting
- A shaped replacement lamp
- Long life
- Dimmable

This item has been discontinued.
Possible replacement:

- [S9840](#)

Compatible Dimmers

- Lutron® Ariadni AYCL
- Leviton® 6674
- Cooper® TAL06P-C1
- Lutron® Nova T NTCL-250
- Lutron® Caseta PD-6WCL



S9216

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9216	045923092166	120	9.8	60W	A19	GU24	GU24

Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
9.8A19/OMNI/300/LED/2700K/GU24	Dimmable	Frosted	4-1/2"	2.38"	810	25000	2700

Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	ENERGY STAR	RoHS Compliant
Warm White	80	300	Operating temperature: -20°C (-4°F) to a maximum of +45°C (113°F)	24/6	Box	ENERGY STAR	Yes

UL or ETL Listed	UL Classification	Warranty	Status	Suggested Substitute
Yes	cULus - Listed	3 Year Limited	Discontinued	S9840



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051