

TF6031VB  
Tiffany Table Lamp  
Vintage Bronze  
Flowered Ladybug



DIMENSIONS

Dimensions: 7" W x 4" H x 6" D  
Overall Height: --  
Backplate Dimensions: --  
Canopy Dimensions: --  
Chain/Downrod Length: --  
HCWO: --  
Weight: 1.76 lbs  
Dimensional Weight: 3.00 lbs.

QUOIZEL.

DETAILS

Material: STEEL  
Glass/Shade Description: - Tiffany Glass  
Shade 2 Description: --  
Shade 3 Description: --

LAMPING

Light Source: Incandescent  
Bulb Included: Yes  
Bulb Type: Candelabra Base  
Bulb Quantity: 1  
Watts per Bulb: 7  
Diffusers: --

PHOTOMETRICS

LED  
Lumens: --  
Color Rendering: --  
Color Temperature: --

ELECTRICAL

Dimmable: --  
Voltage: 120v W/No Transformer  
Wire Length: 6'

INSTALLATION

ADA: --  
Location Rating: --  
Install Position: --  
Sloped Ceiling Compatible: --

We reserve the right to revise the design of components of any product due to parts availability or change in our Listed Mark standards without assuming any obligation or liability to modify any products previously manufactured and without notice. This literature depicts a product DESIGN that is the SOLE and EXCLUSIVE PROPERTY of Quoizel Lighting Inc. Compliance with U.S. COPYRIGHT and PATENT requirements, notification is hereby presented in this form that this literature, or this product depicts, is NOT to be copied, altered or used in any manner without the express written consent of, or contrary to the best interests of Quoizel Inc. 03/31/2013