

Electrical Commercial and Industrial

Products | Documentation & Literature | News & Tradeshows | Support

United States > Energy > Electrical Commercial and Industrial > Products > Electrical Commercial & Industrial Products Catalog > Terminals, Kits and Tools > Terminals > 3M™ Highland™ Vinyl Insulated Ring Terminal RV10-10Q, AWG 12-10, 25/bag

[Find An Account Rep](#)

[Where To Buy \(Find A Distributor\)](#)

[Contact Us](#)

3M™ Highland™ Vinyl Insulated Ring Terminal RV10-10Q, AWG 12-10, 25/bag

3M ID 80611602931 UPC# 00051128600320 Part Number RV10-10Q

• [Print](#)



3M™ Highland™ Ring Tongue Terminal ensures an ideal fit while offering reliable and safe performance. The terminal has a vinyl-insulated, butted-seam barrel and withstands temperatures of -40 to 221 degrees F (-40 to 105 degrees C). Electrolytic copper construction offers good conductivity and a tin-plated finish resists corrosion.

- Yellow vinyl-insulated, butted-seam barrel ensures a secure fit and offers reliable performance
- Funnel-designed, polyvinyl chloride sleeve offers easy insertion of wires
- Standard-style ring tongue fits around the stud
- Stud size #10
- Accommodates wire sizes 12 to 10 AWG
- Made of electrolytic copper for good conductivity and has tin plating for corrosion resistance
- Withstands a temperature range of -40 to 221 degrees F (-40 to 105 degrees C)
- 600V-rated for building wire and 1000V for signs, fixtures or luminaires
- UL Listed, CSA Certified and RoHS 2011/65/EU Compliant
- 25/bag

Need Help?

ire

Questions?

We can help

[Contact Us](#)

Overview	Documents
A ring is the standard style of tongue. The safest and most reliable; it cannot be removed unless mounting screw is removed.	
Specifications	
Agency Approvals	UL and CSA
Barrel Length	0.25 Inch
Barrel Style	Butted
Brand	Highland
Clearance (C)	0.29 Inch
Conductor Size	12 - 10 AWG
CSA File Number	LR22190
Dimension E	0.84 Inch
Insulation Material	Vinyl
Length	1.03 Inch
Maximum Insulation Outer Diameter	0.25 Inch
Packaging	25 per bag
RoHS 2011/65/EU Compliant	Yes
RoHS EU Comments	RoHS 2011/65/EU compliant without exemption *Important RoHS information
Stud Size	10
Terminal Style	Standard
Terminal Type	Ring

Thickness	0.04 Inch
Trademark	Highland
UL File Number	E23438
Width	0.38 Inch

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

Note: 3M products offered on a government contract that require country of origin representation must be certified by 3M Trade Compliance. Contact customer service at 800-245-3573 to request a certificate.