



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Quicklag Industrial Thermal-Magnetic Circuit Breaker

**BAB3070HS**

**UPC:** 786679509692

**Dimensions:** 4 IN \* 3.8 IN \* 3.4 IN (L \* W \* H)

**Notes:** HACR rated

**Warranty:** 1 year

### Specifications:

- **Special Features:** 120V, 208V, 240V shunt trip
- **Type:** Quicklag
- **Quantity:** 8
- **Mounting:** Bolt-on
- **Circuit Breaker Type:** BAB
- **Trip Type:** Non-Interchangeable
- **Amperage Rating:** 70A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 240V

### Supporting documents:

- [Eaton's Volume 4-Circuit Protection Catalog](#)
- [Eaton Specification Sheet - BAB3070HS Specification](#)

### Certifications:

- UL Listed
- CSA Certified

**Product compliance:** No Data

