

LED InstantFit Lamps

17T8/48-5000 IFG 10/1

Philips LED T8 InstantFit Lamps are an ideal energy saving choice for existing linear fluorescent fixtures.

Product data


General Information		Voltage (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	120-277 V	
Main Application	Industrial	Temperature	
Nominal Lifetime (Nom)	36000 h	T-Ambient (Max)	35 °C
Switching Cycle	50000X	T-Ambient (Min)	-20 °C
B50L70	36000 h	T-Storage (Max)	65 °C
Light Technical		T-Storage (Min)	-40 °C
Color Code	850 [CCT of 5000K (2)]	T-Case Maximum (Nom)	60 °C
Beam Angle (Nom)	240 °	Controls and Dimming	
Luminous Flux (Nom)	2100 lm	Dimmable	No
Luminous Flux (Rated) (Nom)	2100 lm	Mechanical and Housing	
Rated Beam Angle	240 °	Product Length	1200 mm
Correlated Color Temperature (Nom)	5000 K	Approval and Application	
Color Consistency	<6	Energy Saving Product	Yes
Color Rendering Index (Nom)	82	Suitable For Accent Lighting	No
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Efficiency Label (EEL)	A+
Operating and Electrical		Approval Marks	CE marking UL certificate RoHS compliance KEMA Keur certificate
Input Frequency	50 to 60 Hz	Energy Consumption kWh/1000 h	20 kWh
Power (Rated) (Nom)	17 W		
Starting Time (Nom)	0.5 s		
Warm Up Time To 60% Light (Nom)	instant full light		
Power Factor (Nom)	0.9		

LED InstantFit Lamps

Product Data	
Order product name	17T8/48-5000 IFG 10/1
EAN/UPC - Product	046677456573
Order code	929001151204
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	10
Material Nr. (12NC)	929001151204
Net Weight (Piece)	0.001 kg

Dimensional drawing



LEDtube 1200mm 17W G13/850

Product	D1	D2	A1	A2	A3
17T8/48-5000 IFG 10/1	25.68 mm	28 mm	1198.0 mm	1205.0 mm	1212.0 mm

