

Hendrik Collection
Hendrik 1 Light Wall Sconce - NI
5076NI (Brushed Nickel)



Dimensions

Height	12.00"
Width	5.25"

Alternate Lamps

Lamp Included	Bulb Listing	Light Source	Max Wattage/Range	Bulb Product ID	Dimming
No	Hybrid	CFL	18-25W		

Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____

Ordering Information

Product ID	5076NI
Finish	Brushed Nickel
Available Finishes	CH, NI, OZ
Collection	Hendrik Collection

Dimensions

Extension	8.00"
Height from center of Wall opening	6.00"
Base Backplate	4.50 X 12.00
Weight	2.50 LBS

Specifications

Material	Steel
Glass Description	Satin Etched Cased Opal

Electrical

Voltage	120V
---------	------

Qualifications

Safety Rated	Damp
Warranty	www.kichler.com/warranty

Installation

Install Glass Up or Down	Yes
--------------------------	-----

Primary Lamping

Light Source	Incandescent
Lamp Included	Not Included
Number of Lights/LEDs	1
Max or Nominal Watt	100W
Socket Wire	150
Socket Type	Medium
Lamp Type	A19