



S9252

6.5A19/CL/LED/E26/27K/120V
6.5 watt A19 LED; Clear; Medium base; 2700K; 810 lumens;
120 volts

Features

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 60 watt lamps
- Long life - 15,000 hours
- Damp Location
- UL listed for totally enclosed fixtures
- Shatterproof coated

When used with incandescent dimmers, derate the dimmer's maximum load by 75%. Consult your local electrical code to ensure compliance.

This item has been discontinued.

Suggested replacement:

- [S9562](#)

Compatible Dimmers

- Cooper TAL06P-C1
- Leviton 6674



S9252

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9252	045923092527	120	6.5	60W	A19	Medium	E26

Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
6.5A19/CL/LED/E26/27K/120V	Dimmable	Clear	4 1/8"	2.38"	810	15000	2700

Color	CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant	UL or ETL Listed	UL Classification
Warm White	80	360	24/6	Box	Yes	Yes	cRU - Recognized Component

Warranty	Status	Suggested Substitute
3 Year Limited	Discontinued	S9562



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051