



S9406

7PAR20/LED/40'/3000K/120V/D
7 watt PAR20 LED; 3000K; 40' beam spread; Medium base;
120 volts

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- Approved for enclosed fixtures
- For Indoor and Outdoor use
- Dimmable

Compatible Dimmers

- Leviton 6674
- Leviton IPL06-10
- Lutron NTCL-250
- Lutron PD-6WCL
- Lutron SELV-300P
- Lutron SLV-600P



S9406

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9406	045923094064	120	7	50W	PAR20	Medium	E26

Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
7PAR20/LED/40'/3000K/120V/D	Dimmable	Silver	3-1/32"	2.50"	500	25000	3000

Color	CRI	Beam Spread Deg	Pack	Package Type	ENERGY STAR	RoHS Compliant	Fixture Type
Warm White	80	40	24/6	Box	ENERGY STAR	Yes	Enclosed Rated

UL or ETL Listed	UL Classification	Warranty
Yes	cULus - Wet Location Rated	3 Year Limited



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051