



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Type CHQ 3/4-inch Classified Replacement Breaker

CHQ115

UPC:782113010816

### Dimensions:

- **Height:** 3 IN
- **Length:** 2.5 IN
- **Width:** .8 IN

**Weight:** .3 LB

**Notes:** Replacement for Square D Type QO Breakers. Requires one 3/4-inch (19.1 mm) space.

### Warranties:

### Specifications:

- **Amperage Rating:** 15A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120/240V
- **Main Circuit Breaker:** CHQ
- **Wire Size:** (1) #14-8, (2) #14-10 AWG Cu/Al  
60°C or 75°C
- **Used With:** Type CH Loadcenters

### Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CHQ115](#)

### Certifications:

- UL 489

**Product compliance:** No Data

