

GFNT2



Color:  Brown

UPC Code: 07847771273

Country Of Origin: China

NEMA:
5-20R



GFNT2

Brand Features

Peace of mind, all the time. The SmartlockPro Self-Test GFCI tests itself even if you forget. Designed to meet the latest UL standard for auto-monitoring (self-test) our complete line of self-test GFCIs periodically conduct an automatic internal test to confirm that it can respond to a ground fault. With the slimmest profile on the market, the device allows for fast and easy installation, while Leviton's patented reset lockout mechanism prevents reset of the GFCI if it is not wired or operating correctly. The SmartlockPro Self-Test GFCI is the smart choice in ground fault circuit interrupter protection.

Item Description

20 Amp, 125 Volt Receptacle/Outlet, 20 Amp Feed-Through, Self-test SmartLock Pro Slim GFCI, monochromatic, Residential/Commercial applications, back and side wired, heavy duty, wallplate/faceplate and self grounding clip included - Brown

Technical Information

AC Horsepower Ratings

At Rated Voltage: 1 HP

Electrical Specifications

Dielectric Voltage: Withstands 1250VAC per UL 943 and CSA-C22.2 No. 144.1-06

Temperature Rise: Max 30C after 100 cycles OL at 150 percent rated current

Short Circuit Current Rating: 10KA

Environmental Specifications

Operating Temperature: -35C to +66C

Flammability: Rated V-2 per UL94

Material Specifications

Face Material: Thermoplastic

Body Material: Polycarbonate

Terminal Screws: Plated Steel

Line Contacts: Brass Triple-Wipe .031 Thick

Yoke: Zinc-Plated Steel

Grounding Screw: Plated Steel

Clamps: Brass

Notes: w/ Wallplate

Mechanical Specifications

Product ID: Ratings are permanently marked on device

Terminal ID: Brass-Hot, Green-Ground, Silver-Neutral

Terminal Accom.: 14-10 AWG

Product Features

Strap Material: Galvanized Steel

Face Material: Thermoplastic

Grounding: Self-Grounding

Warranty: 2-Year Limited

Color: Brown

Trip Level: Class A, 5mA plus or minus 1mA

Termination: Back & Side

Grade: Commercial

Wire: 3

Feature: Self-Test

NEMA: 5-20R

Body Material: Polycarbonate

Voltage: 125 Volt

Amperage: 20 Amp

Standards and Certifications: UL/CSA

Fed Spec WC-596: Yes

Pole: 2

Notes: w/ Wallplate

Standards and Certifications

CSA C22.2 No. 42: Yes

UL 943: File E48380

MIL-SPEC: A-A-55459-SB

CSA-C22.2 No. 144.1-06: File LR-57811

Fed Spec WC-596: Yes

ANSI: C-73

UL498: Yes

NOM: Yes

NEMA: WD-6

Features and Benefits

- Provides continuous ground fault protection – detects and trips on actual ground fault even when self-test is being conducted
- On initial power up, tests the GFCI within 3 seconds
- Auto-monitoring exceeds the UL requirement
- Auto adapts and shifts to more frequent testing if potential problem is detected
- Status Indicator Light provides simple, intuitive feedback on power and protection status as well as indication of line/load reversal
- Patented Lockout Action prevents reset if GFCI is damaged and cannot respond to a ground fault
- Electronics are designed to minimize any false triggers
- Reduced depth makes it easier to install in any electrical box, even shallow ones
- Terminals allow for easy wiring options – back and side wire capable
- External back wire clamps provide visual indication of proper wire seating
- Withstands high torque and resists wire pullout
- Standard brass self-grounding clip
- Trip threshold meets or exceeds UL requirements for tripping time
- Improved immunity to high-frequency noise reduces nuisance tripping
- Advanced electronics design provides superior resistance to electrical surges and over-voltages
- Compatible with all Decora devices and wallplates; available in select Decora colors
- UL Fed Spec WC-596 rated

SPECIFICATION SUBMITTAL

JOB NAME: 	CATALOG NUMBERS: 	
JOB NUMBER:		

Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747

Teléfono: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.T. Monday-Friday): +1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-469-7890 ·

FAX: +1-800-824-3005 · www.leviton.com/canada

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)5386-

1797 · www.leviton.com.mx

Visit our Website at: www.leviton.com

© 2012 Leviton Manufacturing Co., Inc. Todos los derechos reservados. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/international/contacts/

