

UNDERCABINET | 24VDC LARC5 DIMMABLE LED LIGHTBAR



PRODUCT DESCRIPTION

LARC5 24VDC Architectural LED Linear Lightbar is a 8", 16", 24" or 32" brushed aluminum, rigid and unobtrusive (only 5/8" thickness) dimmable LED Lightbar that utilizes a dense array of strategically placed LEDs. LARC5 can be interconnected in series from one 24VDC power source. Only 3.9W for 8", 7.8W for 16", 11.7W for 24" and 15.6W for 32". 50,000 hour LED life. Designed for cove lighting, commercial and architectural applications. Frosted lens assures an even glow over the length of the fixture with no visible diode imaging.

PROJECT	ТҮРЕ
CATALOG NUMBER	

KEY FEATURES

- Unique design extruded aluminum vessel with polycarbonate lensing
- No visible diode imaging reflected on highly polished surfaces
- Diodes shielded by white frosted polycarbonate lensing
- · 3M double stick tape affixed at back
- · Class 2. Maximum run on a given lead is 20'.
- · Connectors available (see below)
- Dimmable. For a complete list of applicable dimmers, please consult product page on website.

ELECTRICAL

- 24VDC Rated at 6.0W per foot
- 8": 3.9W, 16": 7.8W, 24": 11.7W, 32": 15.6W
- Rated life: 50,000 hrs.

- 3000K 80+ CRI
- Up to 728 lumens per bar

CERTIFICATION

• ETL

WARRANTY

• 5 year warranty














FIXTURE ORDERING INFORMATION

Catalog No.	Length	Wattage	Lumens	CRI	Kelvin Temp.*	Finish
LARC5-8-30	8"	3.9W/bar	182/bar	+08	3000K	Brushed Aluminum
LARC5-16-30	16"	7.8W/bar	364/bar	80+	3000K	Brushed Aluminum
LARC5-24-30	24"	11.7W/bar	546/bar	+08	3000K	Brushed Aluminum
LARC5-32-30	32"	15.6W/bar	728/bar	+08	3000K	Brushed Aluminum

Includes attached 3M double stick mounting tape, (2) mounting clips with screws, (1) lightbar to power supply connector (LARC5-PS-24) included with each lightbar.

* Kelvin temperature (color) ±200K

ACCESSORY ORDERING INFORMATION

Cat. No.	Description
LARC5-BB-4	4" flexible lightbar to lightbar connector
LARC5-BB-12	12" flexible lightbar to lightbar connector
LARC5-BB-24	24" flexible lightbar to lightbar connector
LARC5-BB-36	36" flexible lightbar to lightbar connector
LARC5-BB-60	60" flexible lightbar to lightbar connector

Cat. No.	Description
LARC5-PS-24	24" flexible lightbar to power supply connector
LARC5-PS-48	12" flexible lightbar to power supply connector
LARC5-PS-60	24" flexible lightbar to power supply connector
GMSB-W	Splice box - white - 2"L x 1"W x 5/8"D
GMSR_R	Splice hoy - black - 2"L v 1"W v 5/8"D

POWER SUPPLIES

PHOTOMETRICS

· Please see our website at gmlighting.net

· Please see our website at gmlighting.net



9830 W. 190th Street, Unit F Mokena, IL 60448

Toll-Free: (866) 671-0811 FAX: (708) 478-2640

www.gmlighting.net sales@gmlighting.net

