

# RTB Cord Reel Series, NEMA 2 (indoor) or NEMA 4 (outdoor) Rated



## RTB Industrial Grade Retractable Power Cord Reels

NEMA 4 rated for indoor and outdoor environments, including wet locations.

Cord reels are de-rated to NEMA 2 when adding an accessory (plugs, outlet boxes, etc).

*\* Note: All RTB cord reels are built to UL/CSA standards however not all configurations are third party listed.*

### Cord Reel Features:

- **NEW!** Cord reels available in safety yellow, white or matte black powder coat
- All steel construction, including mounting base
- Slip Ring rated for 600 Volts/30 Amps
- 12 position adjustable guide arm
- Adjustable ratchet can be engaged (positive lock) or disengaged (constant tension) as needed
- Adjustable ball stop included
- 6' Feeder Cord included
- Made in USA

### Options:

- 2 – 4 Conductors
- 12 – 16 AWG
- SJOW, SOOW, SEOW
- Standard cord lengths are shown below, custom cord lengths available upon request
- Optional Pivot Base rotates up to 345°
- Optional Swivel Base for 360° continuous motion

**Custom configuration is available!** If you don't see what you're looking for, [contact us](#) or call (716) 312-0088 to design a solution for you.