

Electrical Commercial and Industrial

Products | Documentation & Literature | News & Tradeshows | Support

[United States](#) > [Energy](#) > [Electrical Commercial and Industrial](#) > [Products](#) > [Electrical Commercial & Industrial Products Catalog](#) > [Terminals, Kits and Tools](#) > [Terminals](#) > 3M™ Scotchlok™ Block Fork Vinyl Insulated, 50/bottle, MV10-6FBX

[Find An Account Rep](#)



[Where To Buy \(Find A Distributor\)](#)

[Contact Us](#)

3M™ Scotchlok™ Block Fork Vinyl Insulated, 50/bottle, MV10-6FBX

3M ID 80611464100 UPC# 00051128587645 Part Number MV10-6FBX

• [Print](#)



3M™ Scotchlok™ Color-Coded Block Fork is a lug connection terminal that ensures an ideal fit while offering reliable and safe performance. The terminal has a vinyl-insulated, brazed-seam barrel and withstands temperatures of -40 to 221 degrees F (-40 to 105 degrees C). Electrolytic copper construction offers good conductivity and a tin-plated finish resists corrosion.

- Yellow vinyl-insulated, brazed-seam barrel ensures a secure fit and offers reliable performance
- Funnel-designed, polyvinyl chloride sleeve offers easy insertion of wires
- Suitable for use in a terminal block
- Stud size #6
- Accommodates wire sizes 12 to 10 AWG
- Electrolytic copper construction offers good conductivity
- Withstands a temperature range of -40 to 221 degrees F (-40 to 105 degrees C)
- 600V-rated for building wire and 1000V for signs, fixtures or luminaires
- UL Listed, CSA Certified and RoHS 2011/65/EU Compliant
- 50/carton, 500/case

Need Help?

Questions? We can help [Contact Us](#)

Overview	Documents
<p>3M™ Scotchlok™ Block Fork Terminal is color-coded for quick and easy identification of the wire size required. It has a brazed-seam barrel that is covered by a funnel-designed, rigid-molded, polyvinyl chloride sleeve to guide the wire into position while providing electrical contacts and mechanical stress relief at the point of insulation. The abrasion-resistant, flared, vinyl-sleeve insulation ensures easy crimping. UL Listed, CSA Certified and RoHS 2011/65/EU Compliant.</p>	
Specifications	
Agency Approvals	UL and CSA
Barrel Style	Brazed
Brand	Scotchlok
Clearance (C)	0.29 Inch
Conductor Sizes	12 - 10 AWG
CSA File Number	LR22190
Dimension E	0.84 Inch
Insulation Material	Vinyl
Length	1.03 Inch
Maximum Insulation Outer Diameter	0.250 Inch
Packaging	50 per bottle
RoHS 2011/65/EU Compliant	Yes
RoHS EU Comments	RoHS 2011/65/EU compliant without exemption *Important RoHS information
Stud Size	6
Terminal Style	Block
Terminal Type	Fork
Thickness	0.04 Inch

Trademark	Scotchlok
UL File Number	E23438
Width	0.32 Inch

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

Note: 3M products offered on a government contract that require country of origin representation must be certified by 3M Trade Compliance. Contact customer service at 800-245-3573 to request a certificate.