



S2422

60T9/CL/12S/120V/Vintage
60 watt T9 Incandescent; Clear; 3000 average rated hours; 230 lumens; Medium base; 120 volts

Features

- Vintage Style incandescent
- Historic restoration quality
- Classic, warm glow



S2422

Item Number	UPC	Watts	Lamp Shape	Base	ANSI Base	Lamp Code	Voltage
S2422	045923024221	60	T9	Medium	E26	60T9/CL/12S/120V/Vintage	120
Kelvin Temp	Color	Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Average Rated Hours
2700	Warm White	Clear	7-5/16"	1-3/32"	Hairpin	240	3000
Pack	Package Type	Dimmable/Non-Dimmable		CEC Status		RoHS Compliant	
50/10	Box	Dimmable		Lawful for sale in California		Yes	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

