



*max overall height

Measurements:

<u>Height</u>	<u>Width</u>	<u>Length</u>	
6.75"	24.00"	24.00"	
<u>Max OAH</u>	<u>Min OAH</u>		
118.00"	9.50"		
<u>Hanging Weight</u>	<u>Canopy Width</u>	<u>Canopy Height</u>	<u>Canopy Length</u>
33.00 lb	7.08"	1.57"	7.08"

Lamping:

LED PCB LED	3,136 Rated Lumens
16.00 2.8W PCB LED	3000 Color Temperature
44.8 total watt	80+ CRI
Dimmable : Standard Triac/Lutron® or Leviton® CL	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
38.81 lb	27.17"	7.09"	27.17"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209122970	Yes	

Finish:
Bronze BZ

Glass:
Scotch Crystal SH

Material:
Steel + Crystal

Certification:
Dry Location

Additional:
PCB LED (Included)