



S4613

75T4/CL/G8

75 watt; Halogen; T4; Clear; 2000 Average rated Hours; 1250 Lumens; Bi Pin G8 base; 120 volts


Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output



S4613

Item Number	UPC		Watts	Voltage	Lamp Shape	Base	ANSI Base	Lamp Code
S4613	045923046131		75	120	T4	Bi Pin G8	G8	75T4/CL/G8
Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Kelvin Temp	Color	Average Rated Hours	
Clear	2-9/32"	0.50"	CC-8	1250	2900	Warm White	2000	
Pack	Package Type		Dimmable/Non-Dimmable				RoHS Compliant	
960/48	Box		Dimmable				Yes	



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

