



*Hoffman*

## COMLINE OSP Package, Type 4X

Catalog Number: ECL906050P  
US List Price (USD): \$2,392.00

### Bulletin Number:

- DCOM

### Material:

- Aluminum

### RoHS Flag:

- No

### Model Code:

- 17027

### Ship Wt. Std. Pkg. (lbs):

- 80.0

### Interchangeable:

- False

### IP Rating:

- IP66

### Industry Standards:

UL 508A Listed; Type 3, 3R, 4, 4X, 12; File No. E61997 CSA: Type 3, 3R, 4, 4X, 12 NEMA/EEMAC Type 3, 3R, 4, 4X, 12 EC60529, IP66 Designed to meet Telcordia NEBS™ GR-487, GR-63 and IEC 48D EIA 310-D with 19 in. spacing for rack equipment Meets BICSI TDMM, Tenth Edition, Chapter 7, Telecommunication Enclosures (TE) Cabinet is RoHS compliant *NEBS is a trademark of Telcordia*

## Description

---

### Finish:

RAL 7035 light-textured low-gloss polyester urethane powder coating over iron-phosphate-treated surface. Custom finishes available: consult your local Hoffman sales office.

### Application:

A complete, off-the-shelf package for 19-in. rack equipment, lightweight COMLINE™ OSP Wall-Mount Cabinets are constructed of corrosion-resistant aluminum with a foam-in-place gasket that secures and protects sensitive equipment in outdoor applications. Available with or without back-up battery compartment.

### Specifications:

- Rack angles have EIA universal standard square hole spacing
- Eighth-inch thick, depending on cabinet size
- Seams continuously welded and ground smooth for a finished appearance
- Body includes studs for ground bar and rear mounting studs for wood panel

### Features:

- Solar shield helps keep enclosure interior cool when cabinet is installed outdoors and directs liquids away from cabinet opening; can be removed for indoor installations
- Foam-in-place gasket provides environmental seal
- Padlocking L-Handle provides a tight, secure door seal
- Doorstop holds door in place during service for easier and faster maintenance
- Heavy-duty hinged door is easily removed to facilitate equipment installation and removal. Maximum door load 50 lb. (22.7 kg)

- Rack angles adjustable front-to-rear of cabinet
- Gland plates available with cutouts that fit Hoffman T15, T20 and CR23 air conditioners and Hoffman XR20 and XR29 heat exchangers (Indoor use only)
- Radius corners on cabinet eliminate sharp edges
- Stainless steel fasteners resist corrosion to maintain professional appearance
- Pole mounting kits available for all sizes
- Pad mounting plinth available for 600mm deep cabinets
- Battery compartment has front vented captivated door.
- Note – SR20 and SR2 are for indoor use only.

### Technical Data

---

#### COMLINE OSP Package, Type 4X

<b>Catalog Number</b>	<a href="#">ECL906050P</a>
<b>A in.</b>	35.43
<b>B in.</b>	23.62
<b>C in.</b>	19.68
<b>Rack Units</b>	18
<b>P in.</b>	30.47

## Certifications

---



EU Certification

## Documents

---



Instruction Manual



2D DXF CAD



3D STEP CAD




















Spec Sheet



Dimension Drawing

## Accessories

Item	Mounting Panel	EP8060AL
	Wood Panel	E90P60W
	Rack Angles	ERA199S
	Vertical Pole-Mount Channel	EPMC9
	Gland Plate	EGPS2
	Gland Plate	EGPACT15
	Gland Plate	EGPACT20
	Gland Plate	EGPACCR23
	Gland Plate	EGPHX20
	Gland Plate	EGPHX29
	Handle Options	ELHP
	Handle Options	EPL4
	Handle Options	DL36
	Clip Nut Package	AN1032
	Clip Nut Package	ANM5
	Screw Packages	AS1032
	Screw Packages	ASM5
		



Mild Steel Mounting Foot Kit

CMFK



Stainless Steel Mounting Foot Kit

CMFKSS



Composite Mounting Foot Kit

CMTGFT



Wall Mounting Bracket

EMB1



Ground Buss

EGBB1



Ground Buss

EGBB2