



## 5' ALTERNATING USB STEEL PLUGMOLD®; MULTIOUTLET SYSTEM

BK20GB509TRUSBA, G20GB509TRUSBA, S20GB509TRUSBA,  
V20GB509TRUSBA, WH20GB509TRUSBA | [Wiremold](#)

### FEATURES & BENEFITS

Available in 5' (1.5m) length with 9" spacing. 15A tamper-resistant receptacles. 3-wire, #12 THHN (1 hot, 1 neutral and insulated ground conductor). .040" (1.0 mm) steel housing. Packed two per carton. Each unit supplied with one (1) Coupling and two (2) Blank End Fittings. USB is 2.4 Amps (shared between two ports) 5VDC. Please note the charging load on one module will not affect the charging performance of the other USB modules in the product.

- **USB charging.** Dual-port charging modules share 2.4 amps of charging capacity and can charge multiple phones, tablets or other mobile devices at the same time.
- **Multiple colors and finishes.** Painted finishes of black, gray, ivory, and white, as well as anodized aluminum and stainless steel versions integrate easily with any room decor.
- **Compact design.** Low-profile design installs in tight locations while offering multiple power and USB charging connections. Receptacle spacing accommodates bulky AC adapters.
- **Tamper-resistant receptacles.** Prevents the insertion of foreign objects into receptacles reducing the risk of shocks or electrocution. Meets 2014 NEC section 406 requirements.

### SPECIFICATIONS

#### GENERAL INFO

Available Colors: Black, Gray, Stainless, Ivory, White  
Product Series: 20GB509TRUSB  
Component Type: Raceway Base & Cover  
Special Features: Tamper-Resistant

#### TECHNICAL INFORMATION

Material: Steel

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant

