



*max overall height

Measurements:

<u>Height</u>	<u>Width</u>	<u>Length</u>	
2.25"	19.50"	19.50"	
<u>Max OAH</u>	<u>Min OAH</u>		
118.00"	23.62"		
<u>Hanging Weight</u>	<u>Canopy Width</u>	<u>Canopy Height</u>	<u>Canopy Length</u>
6.61 lb	6.25"	1.50"	6.25"

Lamping:

LED PCB LED	630 Rated Lumens
1.00 9W PCB LED	3000 Color Temperature
9 total watt	80+ CRI
Dimmable : Standard Triac/Lutron® or Leviton® CL	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
10.76 lb	23.23"	5.91"	23.23"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209122888	Yes	

Finish:

Polished Chrome PC

Glass:

Beveled Crystal BC

Material:

Steel + Crystal

Certification:

Dry Location

Additional:

PCB LED (Included)