

QUOIZEL

Artisans in Lighting...since 1930

Alcott

Item #TFAT9362VA

Product Category: Floor Lamp

Finish: Bronze

Suggested Rooms: Den, Den, Dining Room

Height: 62.00"

Width: 20.50"

Depth: 20.50"

Item Weight: 22.30 lbs

Packed Weight: 28.00 lbs

Dimension Weight: 38 lbs



Description

The Alcott Tiffany floor lamp features Mission style at its finest. The beautiful shade is artfully arranged and features a soft green stripe accent. The classic base is finished in Valiant Bronze.

Special Features

Glass color in Tiffany lighting products vary in color. No two pieces are identical.

Bulb Type: 2-100W Medium Base or 23W CFL Bulb(s)
Not Supplied

Base Material: ZINC

Listed Mark Rated For: Portable

Switch Type: Pull Chain Socket (On/Off)

Wire Length: 12 Ft

Voltage: 120

Shade Info: Tiffany Glass Shade

We reserve the right to revise the design of components of any product due to parts availability or change in our Listed Mark standards without assuming any obligation or liability to modify any products previously manufactured and without notice. This literature depicts a product DESIGN that is the SOLE and EXCLUSIVE PROPERTY of Quoizel Lighting Inc. In Compliance with U.S. COPYRIGHT and PATENT requirements, notification is hereby presented in this form that this literature, or the product it depicts, is NOT to be copied, altered or used in any manner without the express written consent of, or contrary to the best interests of Quoizel Inc. 03/31/2013

Quoizel Inc., 6 Corporate Parkway, Goose Creek SC 29445

www.quoizel.com

*distance from wall outlet box to highest point of mounted product

3/27/2017

Quoizel Inc. All Rights Reserved - Designs Protected by Copyright