

Decorator TR 15A Single-Pole Switch/GFCI, White

1595SWTTRWCC4



From the innovator of the product category, comes a full range of Pass & Seymour GFCI receptacles to enhance safety, shorten installation times and increase productivity on the jobsite. Features patented SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to the receptacle is disconnected.

features & benefits

- Protects children: patented shutter system helps prevent improper insertion of foreign objects.
- Meets National Electrical Code® Tamper-Resistant requirements.
- SafeLock™ Protection: if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.
- Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly.
- Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.
- Trip indicator light (red LED).
- Two back wire holes per terminal.
- Side or internal screw-pressure-plate back wire with #10-#14 AWG solid or stranded copper wire.
- Ground screw has a back wire clamp for easy installation.
- 10kA short circuit wiring.
- Mounting screws are shipped captive in the device and wall plate for easier installation.
- High-impact-resistant thermoplastic construction.
- Extra-long strap.
- Button colors match the device face.
- Dual-direction test and reset buttons.
- Class A rated GFCI.
- Supplied with matching TP26 nylon wall plate.
- Tri-drive screws.
- 10kA short circuit rating.
- For covering patents, see www.legrand.us/patents.

specifications

General Info

Color: White
Type: Single-Pole Switch/GFCI
Special Features: Tamper Resistant
Style: Decorator

Listing Agencies/Third Party Information

CSA Standard: C22.2 No. 42, 144, 111
CUL Listing No: E42190
cULus: Yes
cUL Standard: Yes
Federal Spec: Yes
Fed Spec Number: WC596
UL Listing No: UL498
UL Listed: Yes
UL Standard: Yes
UN SPS C: 39121704

Dimensions

Depth U S: 1.13"
Height U S: 4.2"
Length U S: 4.20"
Width U S: 1.72"

Technical Information

Amps: 15A
NEMA Configuration Number: 5-15R
NEMA Rating: Yes
Volts: 125V
Volts A C: 125

Buy American Act Compliance

Country of Origin: CHINA
Buy American Act Status: No