

Main

Application	Replacement
Approvals	Listed to UL 1449 Second Edition and UL 1283 - Meets requirements of ANSI/IEEE C62.41 and C62.45
Includes	Audible alarm (with enable/disable switch)
Marketing Trade Name	Surgelogic
Maximum Surge Current	120kA/Phase
Mounting Type	Panel
Phase	3-Phase
Service Voltage	480Y/277VAC
Short Circuit Current Rating	200kA
Type	EBA
Wiring Configuration	4-Wire

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.