



77064-962: Two Light Ceiling Flush Mount



Collections: Ceiling Flush Mount (Primary)
Albany
Brockton
Holman
Linwood
Northbrook
Pemberton
Sussex
Wellington
Wheaton

Large Two Light Flush Ceiling Fixture in Brushed Nickel Finish with Satin Etched Glass.

The Sussex Collection of lighting fixtures features classic elements of design while keeping pace with today's popular brushed nickel finish. Two light brushed nickel close to ceiling fixture with satin white glass.
Specificaton change effective June 1, 2004.

UPC #:785652770647

Finish: Brushed Nickel (962)

Dimensions:

Diameter: 12 1/2" **Wire:** 6 1/2"
Height: 5 1/2" **Mounting Proc.:** Key Slots
Weight: 3.2 lbs. **Connection:** Mounted To Box

Bulbs:

2 - Medium A19 60w Max. 120v - Not included
2 - LED Medium A19 8w Max. 120v - Not included
2 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

1 Body - Steel - Brushed Nickel

Safety Listing:

Safety Listed for Damp Locations
Safety Listed for Damp Locations

Instruction Sheets:

Bilingual (English - French) (HC-159FB)
Trilingual (English, Spanish, and French) (990C77_-CFM)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Diffuser	Glass	Satin Etched	1				4	9 7/8	1/2			

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85

97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85
--------	---------	--	-----	-------------	------	------	------	-------	-----	------	----

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	77064-962	1	785652770647	13.58	13.58	7.58	0.809	5.4	125	Yes
NJ Pallet		75		48	40	72	80	405		No
NV Pallet		75		48	40	72	80	405		No