



Representative Image

Catalog No. THQB2120GFT

Description: THQB 2P 120/240V 20A GFCI SELF-TEST

UPC No 783164485554

Products > Circuit Breakers > Mini Circuit Breakers & Supplementary Protectors > Q-Line

Miniature Circuit Breakers

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QL breakers are plug-in versions of the Q Line used for connection to load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications.

Descriptors

Category	Q-Line Miniature Circuit Breakers
----------	-----------------------------------

Specifications

Trip Style	Non-Interchangeable
Frame Type	Q-Line
Amperage	20 A
System Voltage	120/240 Vac
Poles	2
Trip Function	LIG
Continuous Current Rated	Standard
120/240 Vac Interrupting Rating	10 KAIC
Suitable for Reverse Feed	Yes
Product Line	TEY / Q-Line (Bolt-On)
Long Time	Fixed
Instantaneous	Fixed
Ground Fault	Yes
Protective Relays	No
Current Metering	No
Special Markings	HACR
GSA Compliance	No

Classifications

UL File #	E51075
-----------	--------