



CONSTRUCTION SPEC GRADE RECEPTACLES, BACK & SIDE WIRE, 20A, 125V, IVORY

CRB53621 | [Pass & Seymour](#)

FEATURES & BENEFITS

Construction Spec Grade Duplex Receptacle, Back & Side Wire, 20amp 125volt, Ivory



- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- 8 hole internal screw-pressure-plate back wire terminals accept #10 - #14 AWG solid or stranded copper or copper-clad conductors.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Ivory
Type: Receptacles
Special Features: Back,Side Wire

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: C22.2 No. 42
CSA Standard: Yes
Federal Spec: Yes
UL Listing No: UL498

UL Standard: Yes
UN SPSC: 39121406

DIMENSIONS

Depth (US): 0.78"
Height (US): 3.281"
Width (US): 1.322"

TECHNICAL INFORMATION

Amps: 20A
NEMA Configuration Number: 5-20R
Volts: 125V
Volts (AC): 125
Capacity: Duplex
Grade Type: Construction

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

