



S9457

15PAR38/LED/60°/3000K/120V/2PK
15 watt PAR38 LED; 3000K; 60° beam spread; Medium base;
120 volts; 2-Pack

Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- For Indoor and Outdoor use
- Non-Dimmable



2 Pack

S9457

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Lamp Shape	Base	ANSI Base
S9457	045923094576	120	15	90W	PAR38	Medium	E26

Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
15PAR38/LED/60°/3000K/120V/2PK	Non-Dimmable	Silver	5-3/16"	4-3/4"	1150	25000	3000

Color	CRI	Beam Spread Deg	Pack	Package Type	RoHS Compliant	UL or ETL Listed	UL Classification
Warm White	80	60	8-2pks	Box	Yes	Yes	cULus - Wet Location Rated

Warranty

[3 Year Limited](#)



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

