



by Schneider Electric

List Price \$1,890.00 USD

Availability **Non-Stock Item: This item is not normally stocked in our distribution facility.**

Technical Characteristics

Circuit Breaker Type	Standard
General Application	Provides overload and short circuit protection
Approvals	UL Listed - CSA Certified - IEC Rated
Catalog Reference Number	0734CT0201
Width	4.50 Inches
AC Magnetic Trip Setting	2400A Fixed Trip (1200A Hold)
Ampere Rating	150A
For Use With	I-Line Panelboards and Switchboards
Frame Type	Q-Frame
Marketing Trade Name	Powerpact
Voltage Rating	240VAC
Mounting Type	I-Line Plug-On
Weight	4 Pounds
Number of Poles	3-Pole
Phase Connection	ABC
Short Circuit Current Rating	65kA@240VAC
Terminal Type	I-Line Connection (ON end) - Lugs (OFF end)
Type	QG
Height	6.47 Inches
Wire Size	#4-300 AWG/kcmil(Al/Cu)
Depth	3.93 Inches

Shipping and Ordering

Category	01023 - Circuit Breakers, Thermal Magnetic & Mag Only, 240 Vac, Type Q2, UL, I-Line
Discount Schedule	DE2
Article Number	785901705604
Package Quantity	1
Weight	6.77 lbs.
Availability Code	Non-Stock Item: This item is not normally stocked in our distribution facility.
Returnability	Y

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.