



Search within category

BUY NOW

DESIGN / INSTALL

LAB750-12-1



Two-hole, aluminum, long barrel, 750 kcmil, 1/2" (12.7mm) stud hole.

Specs Packaging Details Documents

★ Add to Favorites

🛒 Add to BOM

Product Type	Compression Connectors - Lugs
Material	Tin-Plated Aluminum
CSA Certified	Yes
UL Listed	Yes
Length (In.)	7.31
Length (mm)	185.7
Aluminum or Copper Conductor Size	750 kcmil
Stud Hole Size (In.)	1/2
Stud Hole Spacing (In.)	1.75
Tongue Width (In.)	1.72
Barrel Length (In.)	3.42
Angle	Straight
Conductor Material	Aluminum or Copper
Panduit Color Code	Red
Panduit Die Index No.	P125
Part Features	dual rated,prefilled joint compound,enclosed barrel,tin plated to inhibit corrosion
Stud Hole Size (mm)	12.7
Stud Hole Spacing (mm)	44.5
Tongue Thickness	0.56
Tongue Thickness (mm)	14.2
Tongue Width (mm)	43.7
Wire Strip Length (In.)	3 7/16
Wire Strip Length (mm)	87.3
RoHS Compliancy Status	Compliant
Min. Order Qty.	1.0000
Burndy Die Index No.	301
T&B Die Index No.	115

Request a Quote

Are you looking for a free quote on Panduit Products and Solutions?

**Yes, I need a quote! ▶**

Request a Quote  
Are you looking for a free quote on Panduit  
Products and Solutions?

---

**Yes, I need a quote!** ▶