

### Product Description:

4 foot LED T8 system with internal driver. The LED T8 system replaces traditional T8 systems. Comes double ended input.

### Common Technical Data:

Color Temperature	2700K to 5000K
CRI	> 80
Operation Temperature	-20°C to 50°C
Input Voltage	AC100-347V
Frequency	50-60Hz
Power Factor	More than 0.99
Rated Life	50,000 hours
Power Supply Efficiency	90%



### Product Specification:

Product code	Length (ft)	Certificate	Input Voltage	Lumens	Description				
				3000-5000K	CRI	Driver Type	Housing	Wire Input	
ZY-T8-18W1200 BINT	4	UL & DLC listed	AC100-347V	1950 lm	>80	Internal	Aluminum	Two End	
ZY-T8-22W1200 BINT	4	UL & DLC listed	AC100-347V	2700 lm	>80	Internal	Aluminum	Two End	

### Ordering Guide:

ZY	T8	18W/22W	1200	B	I	NT	3000K-5000K
Company Code	Housing Type	Wattage	Length	2835 LED	Internal Driver	Input Type	CCT

### Warranty:

This product has a warranty for a period of 5 years from the date of purchase. The warranty is invalid in the case of improper installation, tampering, or removal of the Q.C. date label. Installation in an improper working environment or installation not according to the current edition of the National Electric Code also invalidates the warranty. Should this product fail during the warranty period, it will be replaced free of charge, subject to correct installation and return of the faulty unit. James® does not accept responsibility for any installation costs associated with the replacement of this product. This warranty is an addition to the statutory rights in the country of purchase. James® reserves the right to alter specifications without prior notice.

[www.JamesLighting.com](http://www.JamesLighting.com)

Contact your Regional Account Manager  
Office: 678-608-2751  
INFO@jameslighting.com



**JAMES LIGHTING**  
**US Regional Office**  
Atlanta, Georgia USA  
© 2016 James Lighting. All Rights Reserved.