

Rittal – The System.

Faster – better – everywhere.

Compact enclosures AE – AE 1039.500

Date : Sep 22, 2017

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Compact enclosures AE – AE 1039.500

created: 22.09.2017 build on www.rittal.com/us-en



Product description

Material:	Housing: Carbon steel Door: Carbon steel, all-round foamed-in PU seal
Surface finish:	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated
Color:	RAL 7035
Protection category IP to IEC 60 529:	IP 66
Protection category NEMA:	NEMA 4
IK code:	IK08
Supply includes:	Housing with hinged door(s), of all-round solid construction Flange (gland) plate(s) in enclosure base Mounting plate Lock: 3 mm double-bit
Base material:	Carbon steel

Product features

Dimensions:	Height: 380 mm (15 ") Width: 600 mm (24 ") Depth: 210 mm (8.3 ")
Material thickness:	Housing: 1.38 mm (0.05 ") Door: 1.5 mm (0.06 ")

Mounting plate: 2.5 mm (0.1 ")

Mounting plate:	Height: 355 mm (14 ") Width: 549 mm (22 ")
Number of doors:	1
Door catch on right, may be swapped to the left:	yes
Lock version:	Cam
No. of locks:	1
Lock Insert:	3 mm double-bit
Flange plate, size:	5
Flange plate, qty:	1
Packaging unit:	1 pc(s).
Weight/packaging unit:	15.4 kg
EAN:	4028177252042
Customs tariff number:	94032080
ETIM 6.0:	EC000261
ETIM 5.0:	EC000261
eCl@ss 8.0/8.1:	27180101
eCl@ss 7.0/7.1:	27180101
eCl@ss 6.0/6.1:	27180101
eCl@ss 5.1/5.1.4:	27180102
Product description (long):	AE Compact enclosure, WHD: 600x380x210 mm, Sheet steel, with mounting plate, single-door, with two cam locks

Approvals

Approvals: Bureau Veritas
CSA
DNV GL

Lloyds Register of Shipping
NA
Russian Maritime Register of Shipping
TÜV UL + C-UL

Certificates:

IK-Code
NA
Protection category

Declarations:

Declaration of conformity
