



GE
Lighting

94546 - GE CFL 23w T3 Spiral

FLE23HT3/2/841

GENERAL CHARACTERISTICS

Base Type	Screw-In
Life in Years	9.1 yr
Rated Life Hours-nominal	10000 h
Base Description	Medium Screw
Product Technology	Compact Fluorescent
Base	E26
Bulb Shape	R30

PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	70
Initial Lumens-nominal	1600 lm
Color Temperature	4100 K

PRODUCT INFORMATION

Product Code	94546
Description	FLE23HT3/2/841
Alternative Unit Of Measure	EACH
Standard Package Quantity	10
Ean UPC	043168945462
Standard Package GTIN	00043168945462
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
Sales Unit	Each
UCC	043168945462
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168945462
Standard Package GTIN	10043168945469
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168945462

ELECTRICAL CHARACTERISTICS

Estimated Energy Cost per Year	2.77 \$
Dimming Capability	No
Rated power (Watts)	23 W